



# ENAPART



93 S Railroad Avenue Unit C  
Bergenfield NJ 07621 USA  
[www.enapart.com](http://www.enapart.com)  
[sales@enapart.com](mailto:sales@enapart.com)



Via del Canneto 35,  
Borgosatollo, Brescia - Italia  
[www.enapart.it](http://www.enapart.it)  
[vendite@enapart.it](mailto:vendite@enapart.it)



Barbaros Mah. Ihlamur Bul. Aĝaoĝlu  
My Newwork No:3/15 Ataşehir / İstanbul  
[www.enapart.net](http://www.enapart.net)  
[satis@enapart.net](mailto:satis@enapart.net)



PRIVADA 10 B SUR #3908 COL.  
ANZUREZ, C.P. 72530, PUEBLA, PUE  
[www.enapart.com.mx](http://www.enapart.com.mx)  
[sales@enapart.com.mx](mailto:sales@enapart.com.mx)



Friedrich-Ebert-Anlage 36, 60325  
Frankfurt am Main, Germany  
[www.enapart.de](http://www.enapart.de)  
[anfrage@enapart.de](mailto:anfrage@enapart.de)



4 boulevard Carnot, 95400  
villiers-le-bel, Paris, France  
[www.enapart.fr](http://www.enapart.fr)  
[sales@enapart.fr](mailto:sales@enapart.fr)



65049, ОДЕСА, ВУЛИЦЯ ІВАНА  
ФРАНКА, БУДИНОК 55, ПОВЕРХ 3  
[www.enapart.com.ua](http://www.enapart.com.ua)  
[sales@enapart.com.ua](mailto:sales@enapart.com.ua)



MUNICIPIUL BUCUREȘTI, SECTOR 3,  
B-DUL BASARABIA, NR.250, CORP P+5  
[www.enapart.ro](http://www.enapart.ro)  
[sales@enapart.ro](mailto:sales@enapart.ro)



〒584-0023 大阪府富田林市若松町  
東2丁目2番16号  
[www.enapart.co.jp](http://www.enapart.co.jp)  
[sales@enapart.co.jp](mailto:sales@enapart.co.jp)



PLAZA NUESTRA SEÑORA DE LAS  
NIEVES 12 ,LOCAL ,50012,ZARAGOZA  
[www.enapart.es](http://www.enapart.es)  
[ventas@enapart.es](mailto:ventas@enapart.es)



Складова база „Онгъл“, Склад А2, п.к.  
4006, гр. Пловдив, България  
[www.enapart.bg](http://www.enapart.bg)  
[sales@enapart.bg](mailto:sales@enapart.bg)



3 Austin Mews, High Street, Hemel  
Hempstead, HP1 3AF , United Kingdom  
[www.enapart.co.uk](http://www.enapart.co.uk)  
[sales@enapart.co.uk](mailto:sales@enapart.co.uk)

## Südmob

Enapart always strives to provide the competitive prices and timings of supplies for its customers. We sell only original equipment and spare parts, although we are not always the official distributor or manufacturer's dealer. All displayed trademarks and part numbers are the property of their respective owners.

### RAND' POUAC'TSrP

UucteBs	'diBuopsocn
<a href="#">0341825</a>	Ohelic,06S97REU 3/97T
<a href="#">034:5 I K.Q1</a>	Oylinder Ooint
<a href="#">0-FQV</a>	-ensor switch
<a href="#">(R) Q2</a>	gripper
<a href="#">(M:4D2Q</a>	hand valve
<a href="#">3R Q2NF24V</a>	0ompact Oylinder
<a href="#">3RK28124V4-</a>	Air Oylinder
<a href="#">:UR Q18K12</a>	Oylinder
<a href="#">-SP42K</a>	E8haust :uffler
<a href="#">-M1K2K4QDMdc4z</a>	solenoid
<a href="#">-M4BK2K4z</a>	z rectangular R97 connector
<a href="#">-MBK2K4QDMdc4z</a>	14Port -olenoid Malve with QDM R0 0oil
<a href="#">0-K1T4P7P</a>	sensor
<a href="#">(R)4FQ</a>	0ompact Air Oylinder with FQmm Vore
<a href="#">0-F2E P</a>	:agnetic Oylinder -ensor -witch
<a href="#">TRKB8ü2</a>	Rual Uod Oylinder with KBmm Vore and ü2mm -troke
<a href="#">bobineGcoil for -M4BK2Q</a>	Ueplacement 0oil for -M4BK2Q -olenoid Malve
<a href="#">:U!Q2F124(4-RQ4AQ</a>	Rual Oylinder H Ohelic
<a href="#">P-74DK42Q</a>	Pressure -witch H Ohelic
<a href="#">P-04DQ42Q47PT</a>	Ohelic
<a href="#">0S4D22</a>	Subricator with KGQL Port -i+e and KB2 cc 0apacity
<a href="#">3TRFQNF24-</a>	pneumatic cylinder @:ÄÄ7ET90 MEU-9/7¼
<a href="#">VCU4Q22 @F22¼</a>	( @:anual drain system¼
<a href="#">-M45K2F4QDMdc4S</a>	-olenoid Malve
<a href="#">TVKB8X1</a>	Pneumatic cylinder
<a href="#">PUCQ18X22</a>	cylinder
<a href="#">VSQ22</a>	Subricator
<a href="#">-"( 2B2D</a>	-traight !nion Citting for Bmm to Dmm Tubing
<a href="#">-"( 252B</a>	-traight !nion Citting for 5mm to Bmm Tubing
<a href="#">3R128F2V</a>	Pneumatic cylinder repair kit
<a href="#">-TIFQIQ1</a>	Oylinder
<a href="#">(M:4D2D</a>	(and operated valve
<a href="#">-:4XK2Q @KQ or QDMdc version¼</a>	solenoid valve
<a href="#">-:4XK2Q @KK2Mac version¼</a>	solenoid valve
<a href="#">-:4XK2Q @QQ2Mac version¼</a>	solenoid valve







<b>Product</b>	<b>Description</b>
<a href="#">QCF-80 - FDA</a>	Flap gasket
<a href="#">2334258</a>	Flap seal
<a href="#">0145805</a>	Joint gasket
<a href="#">SUE0145029</a>	Joint gasket
<a href="#">0145813</a>	Joint gasket
<a href="#">2132039</a>	Gasket kit
<a href="#">2336410, Type: P750, Nominal size: OD 0.50 "</a>	valve
<a href="#">2336412, Type: P750, Nominal size: OD 1.00 "</a>	valve
<a href="#">DIN11851-F50-1.4301</a>	groove nut
<a href="#">DIN11851-F65-1.4301</a>	groove nut
<a href="#">2317012</a>	Flap Gasket
<a href="#">SUE2317014</a>	Flap Gasket
<a href="#">SUE2701902</a>	Rotary actuator
<a href="#">2123266</a>	Block flange for welding
<a href="#">2183873</a>	Blind link complete
<a href="#">S0001521</a>	damper valve
<a href="#">S0001519</a>	damper valve
<a href="#">S0001520</a>	damper valve
<a href="#">2328122</a>	Hyg. Guidance valve
<a href="#">S0005336</a>	Flap Gasket
<a href="#">2307153L</a>	Process control head
<a href="#">0235275</a>	Gasket set
<a href="#">QU01</a>	Gasket set
<a href="#">2012952</a>	Gasket set
<a href="#">2901181</a>	Gasket set
<a href="#">2163015</a>	connection kit
<a href="#">SUE2307101L</a>	Process control head
<a href="#">2153644</a>	damper valve
<a href="#">SUE2025319</a>	Gear lever cl.massif for flaps
<a href="#">2317004</a>	Flap Seal
<a href="#">0102814</a>	Gasket kit complete product. NW 065
<a href="#">2100773</a>	connection kit
<a href="#">0102830</a>	Gasket kit complete drive. DN065/080
<a href="#">SUE2912891</a>	Sealing ring
<a href="#">S0003580</a>	vane valve
<a href="#">2336156</a>	leakage gate valve
<a href="#">2336156-97-00</a>	leakage gate valve
<a href="#">2910123</a>	vane valve
<a href="#">2910121</a>	vane valve
<a href="#">2910047</a>	vane valve
<a href="#">2336405</a>	Disc Check Valve - RV Solid
<a href="#">33501 DN025</a>	
<a href="#">2147844</a>	Mounting kit (feedback unit)

Product	Description
<a href="#">0163147</a>	Valves
<a href="#">0554394</a>	valves
<a href="#">2336153-97-00</a>	leakage gate valve
<a href="#">2336153</a>	leakage flap valve
<a href="#">Seal kit 2308081 (Art. No. 2916295)</a>	non-return valve
<a href="#">Type: P740 / DN 040 - RV Solid (2336499)</a>	Disc check valve
<a href="#">2338078</a>	valve seal
<a href="#">2317007</a>	Flap seal
<a href="#">2317011</a>	
<a href="#">2132550</a>	Top double seat valve complete
<a href="#">S0000114</a>	Klappenteller
<a href="#">P/N: S0000817 Type: K587</a>	flap valve
<a href="#">P/N: 2324362 Type: A372-D-EAF</a>	asept. cross valve
<a href="#">2331023</a>	flap seal
<a href="#">2006913 P/N: M2000 DN 010</a>	svp aseptic angle valve
<a href="#">P/N: 2129836 Type: Modell-2000</a>	aseptic removal valve
<a href="#">2008094</a>	
<a href="#">2008118</a>	DETAY
<a href="#">2106989</a>	Coupling II
<a href="#">2111188</a>	clutch 1 cpl
<a href="#">2153147</a>	clutch-2
<a href="#">2153145</a>	clutch-1
<a href="#">2144108</a>	Gasket set
<a href="#">2144053</a>	Sleeve for SVP valves
<a href="#">2144105</a>	Gasket set
<a href="#">2002388</a>	Gasket set product side
<a href="#">NC DN050-100</a>	rotary drive
<a href="#">2307712</a>	regulating angle valve
<a href="#">2334254</a>	flap seal
<a href="#">SUE2117244</a>	Hose clamp
<a href="#">2331025</a>	
<a href="#">2319121</a>	
<a href="#">repair kit for 2319121</a>	
<a href="#">2105734</a>	o-ring
<a href="#">0924381</a>	o-ring
<a href="#">0925065</a>	o-ring
<a href="#">2147710</a>	threaded plugs
<a href="#">B09585</a>	Seal kit for valve
<a href="#">2003805SP</a>	Pneumatic rotary drive
<a href="#">S0001039</a>	flap valve
<a href="#">2329906</a>	
<a href="#">S374-EAF+ (2324046)</a>	EAF+ overflow valve
<a href="#">2129346</a>	

Product	Description
<a href="#">2154104</a>	
<a href="#">SUE2154101</a>	
<a href="#">2154102</a>	Gasket set product side DN065
<a href="#">2119953</a>	
<a href="#">2317008</a>	flap seal
<a href="#">2317000</a>	flap seal
<a href="#">P/N: 2143030</a>	SVP valve cuff
<a href="#">SUES0003303</a>	flap valve
<a href="#">2311955</a>	flap valve
<a href="#">2132029</a>	
<a href="#">2100533</a>	sealing ring
<a href="#">S390 (2319121)</a>	Hyg Diverter valve - SVP Select
<a href="#">Typ D622 (2308444-05-00)</a>	double seat valve - DSV Complete
<a href="#">2705104 - DN 25-40 / 1"-1.5"</a>	
<a href="#">2019779</a>	Complete gasket set
<a href="#">2336159</a>	leakage flap valve
<a href="#">2336158</a>	leakage flap valve
<a href="#">2122941SP</a>	pneumatic rotary actuator
<a href="#">2317010</a>	Seal for DN 1" valve
<a href="#">0405076</a>	Repair kit Seal set E0205 for valve DN020-DN100
<a href="#">2308573</a>	DN050/2" gasket set
<a href="#">S0001273</a>	valve
<a href="#">SUE2701904</a>	rotary drive
<a href="#">SUE2701905</a>	rotary drive
<a href="#">2155447</a>	Sets of Seals for Aseptic SVP Valves with Diaphragm (P <sup>3</sup> ) and O-Ring
<a href="#">2331027</a>	
<a href="#">2101383</a>	sealing ring
<a href="#">2331026</a>	Flap seal
<a href="#">2101384</a>	sealing ring
<a href="#">2124839</a>	
<a href="#">2124838</a>	
<a href="#">2305527</a>	
<a href="#">2323034</a>	
<a href="#">INTELLITOP 2.0 (2307141L)</a>	process control head
<a href="#">2701918SP</a>	
<a href="#">2550207</a>	Flap valve
<a href="#">2331029</a>	Flap seal
<a href="#">2501602-128-00SP</a>	
<a href="#">2550406</a>	Flap valve
<a href="#">2550408</a>	Flap valve
<a href="#">0896803</a>	Acceptance test certificate
<a href="#">2334185</a>	factory certificate
<a href="#">2148833SP</a>	pneumatic rotary drive



Product	Description
<a href="#">QU01 / Type: K589</a>	flap valve
<a href="#">2501602SP</a>	Pneumatic rotary actuator for flap valves
<a href="#">2501601-128-00SP</a>	rotary drive
<a href="#">2191804</a>	Mounting kit for 2x M12 feedback
<a href="#">2130427</a>	
<a href="#">2122942SP</a>	pneumatic rotary actuator
<a href="#">2334255</a>	
<a href="#">P/N: 2550415 Type: K407</a>	flap valve
<a href="#">2344901</a>	
<a href="#">2312013</a>	
<a href="#">2307151</a>	
<a href="#">2102554</a>	Sealing ring
<a href="#">2159461</a>	Sealing ring
<a href="#">2143033</a>	SVP valve cuff
<a href="#">2307211</a>	
<a href="#">2550221</a>	
<a href="#">2550222</a>	flap valve
<a href="#">2550223</a>	
<a href="#">2029785</a>	
<a href="#">2005489</a>	
<a href="#">2167648</a>	
<a href="#">2146460</a>	
<a href="#">2008763 / T32504</a>	safety valve
<a href="#">2386354 / Type: A804-D</a>	double seat valve
<a href="#">2341600-DE</a>	operating instructions
<a href="#">2142876</a>	
<a href="#">2552612</a>	flapper valve
<a href="#">2552414-128-00</a>	flapper valve
<a href="#">D621/ 2308427</a>	double seat valve
<a href="#">2380200</a>	Asept. Bodensitzventi
<a href="#">2501601-130-00SP</a>	rotary drive
<a href="#">K667/ 2552414</a>	flapper valve
<a href="#">2132531</a>	
<a href="#">2145355</a>	Seal set on product side
<a href="#">S0000521</a>	
<a href="#">SUES0000471</a>	
<a href="#">Type SUE2307101L</a>	
<a href="#">2552511</a>	flapper valve
<a href="#">2308576</a>	
<a href="#">2308592</a>	
<a href="#">2320811</a>	
<a href="#">2320812</a>	
<a href="#">2146012</a>	

<b>Product</b>	<b>Description</b>
<a href="#">2912890</a>	
<a href="#">2501601SP</a>	Pneumatic rotary actuator for flap valves
<a href="#">2550405</a>	flapper valve
<a href="#">2550202</a>	flapper valve
<a href="#">2501602-130-00SP</a>	rotary drive
<a href="#">2550422</a>	flapper valve
<a href="#">2550421</a>	flapper valve
<a href="#">2335630</a>	Hand lever for flap valves
<a href="#">2307111L</a>	Smart head
<a href="#">2551514</a>	Butterfly valve
<a href="#">2307151L</a>	IntelliTop control head
<a href="#">0411512G</a>	
<a href="#">0396705</a>	
<a href="#">2144776</a>	
<a href="#">0481606</a>	
<a href="#">0320473</a>	
<a href="#">2370008</a>	
<a href="#">0963405</a>	
<a href="#">2335924</a>	
<a href="#">2323749</a>	
<a href="#">0396655</a>	
<a href="#">2143030</a>	
<a href="#">2307100</a>	
<a href="#">2131736SP</a>	
<a href="#">2387480-05-00</a>	
<a href="#">2387480</a>	
<a href="#">Type 2132531</a>	
<a href="#">2334350</a>	
<a href="#">0549345</a>	Test valve
<a href="#">2172103</a>	
<a href="#">Type 2350616</a>	gasket kit
<a href="#">2141486</a>	
<a href="#">2387479-01-00</a>	
<a href="#">2387479</a>	
<a href="#">2100531</a>	
<a href="#">2011779</a>	Klappenteller
<a href="#">2317005 - DN 080</a>	flap seal
<a href="#">S0004713</a>	
<a href="#">SUE2132023SP</a>	pneumatic control head
<a href="#">2132549</a>	Complete double seat valve top
<a href="#">2167288</a>	Double seat valve upper part
<a href="#">2313650</a>	Asept. angle valve
<a href="#">2308851</a>	Asept. angle valve

Product	Description
<a href="#">2344995</a>	Asept. Doppeleckventi
<a href="#">2158284</a>	gasket kit
<a href="#">2143031</a>	SVP valve cuff
<a href="#">2338264 / Type: S375-W</a>	Regulating angle valve
<a href="#">SUE2307103L / I903K 2.0</a>	Process control head
<a href="#">SUE2446666</a>	mounting kit
<a href="#">SUE0144980 / Seal for 0452037</a>	Sealing ring for milk pipe screw
<a href="#">2370383 / Seal for 0452037</a>	Sealing ring
<a href="#">2370022 / Seal for 0452037</a>	Sealing ring
<a href="#">2380969</a>	cuff
<a href="#">2550414 / Typ: K407</a>	flapper valve
<a href="#">2912868// 27.00 x 5.00 ( d1 x d2 mm)</a>	O-ring
<a href="#">2370715</a>	
<a href="#">2191039</a>	housing flange intermediate clamp
<a href="#">2340449</a>	valve
<a href="#">2127179</a>	gasket kit
<a href="#">2129417G</a>	
<a href="#">2112118 / gasket kit for NW010 - 020</a>	gasket kit
<a href="#">2380962</a>	
<a href="#">2370812</a>	
<a href="#">2333467</a>	Control valve
<a href="#">2336414</a>	plate check valve
<a href="#">0712133</a>	gasket kit
<a href="#">0528208</a>	Compression spring
<a href="#">2156229</a>	
<a href="#">2159462</a>	O-Ring
<a href="#">QU01 Type: A380-D</a>	
<a href="#">2551406 / Type: K587</a>	valve
<a href="#">2551405 Type: K587</a>	flapper valve
<a href="#">2384600</a>	Hygienic angle seat valve
<a href="#">2322792</a>	
<a href="#">2335847</a>	
<a href="#">2370038</a>	
<a href="#">2308586</a>	
<a href="#">2551407 / Typ: K587</a>	flapper valve
<a href="#">S390 - DN4" - 3x Clamp</a>	Hyg. diverter valve
<a href="#">2132037</a>	
<a href="#">2550205</a>	
<a href="#">QU01/2707118SP</a>	